

### RECONFIGURABLE SEPARATORS FEATURE HOOK AND LOOP FASTENERS









If you require compartmentalized protective organization of your components or equipment, our padded dividers are the right choice. Easily tailored to your needs with repositionable tongue and groove fasteners, our padded dividers are designed to easily organize and protect your equipment.

\*Available for NANUK™ 905 – 960 cases.

### PADDED DIVIDER SET

- A** 1" Thick Nylon Padded Divider Insert
- B** ½" Thick Long Dividers
- C** ½" Thick Short Dividers
- D** 1" Thick Convoluted Foam Pad



MODEL	CONTENTS	STANDARD LAYOUT	MODEL	CONTENTS	STANDARD LAYOUT
<b>905   908</b>	1x Base 2x Long Dividers 1x Short Dividers 1x Convoluted Foam Pad		<b>915   918</b>	1x Base 1x Long Dividers 4x Short Dividers (918 x6) 1x Convoluted Foam Pad	
<b>WEIGHT</b>	<b>905</b> - 0.792lbs   <b>908</b> - 0.999lbs		<b>WEIGHT</b>	<b>915</b> - 1.210lbs   <b>918</b> - 1.797lbs	
<b>920</b>	1x Base 2x Long Dividers 11x Short Dividers 1x Convoluted Foam Pad		<b>923   925</b>	1x Base 4x Long Dividers 10x Short Dividers 1x Convoluted Foam Pad	
<b>WEIGHT</b>	1.562lbs		<b>WEIGHT</b>	<b>923</b> - 1.716lbs   <b>925</b> - 2.552lbs	
<b>930   933</b>	1x Base 2x Long Dividers 13x Short Dividers 1x Convoluted Foam Pad		<b>935</b>	1x Base 2x Long Dividers 8x Short Dividers 1x Convoluted Foam Pad	
<b>WEIGHT</b>	<b>930</b> - 2.629lbs   <b>933</b> - 3.311lbs		<b>WEIGHT</b>	2.486lbs	
<b>940</b>	1x Base 2x Long Dividers 15x Short Dividers 1x Convoluted Foam Pad		<b>945</b>	1x Base 2x Long Dividers 12x Short Dividers 1x Convoluted Foam Pad	
<b>WEIGHT</b>	3.718lbs		<b>WEIGHT</b>	3.949lbs	
<b>950</b>	1x Base 2x Long Dividers 8x Short Dividers 1x Convoluted Foam Pad		<b>960</b>	1x Base Upper tray 2x Long Dividers 9x Short Dividers 1x Convoluted Foam Pad	
<b>WEIGHT</b>	3.905lbs		Lower tray	1x Base 2x Long Dividers 8x Short Dividers 1x Convoluted Foam Pad	
			<b>WEIGHT</b>	6.754lbs	

### Installation

1. Inspect your divider set to ensure that all required parts have been included in the package. Refer to this sheet to find the contents list for your specific case model.
2. The configuration of the dividers within the divider base is customizable to fit your particular items. Refer to this sheet for drawings of the standard layout.
3. Fold all four sides of the base upwards. Attach the corners of the base sides with the hook and loop fastening system.
4. After you have decided on your preferred configuration of the dividers begin by installing the longest dividers. To aid with installation, a piece of loose paper can be positioned between the dividers and the base. Once positioned, remove the paper to attach the hook and loop fasteners. Continue by placing the smaller dividers into position.
5. Once the dividers have been put in place the divider kit can be installed into the case.
6. Complete the installation by installing the convoluted foam in the top of the case.

### Care

If the padded divider set needs to be cleaned, a soft damp cloth with mild soap should be used. Tough stains may require the use of a spot stain remover.